



SERIES: VOF-225A | **DESCRIPTION:** AC-DC POWER SUPPLY


FEATURES

- up to 225 W continuous power
- -40°C to 70°C operating temperature
- industry standard foot print 2" x 4"
- low profile 1"
- power factor correction
- 12 V/0.5 A fan output
- standby power <0.5 W
- efficiency up to 94%
- long life electrolytic capacitors



| MODEL | output voltage | output current | output power ^{1,2} | ripple and noise ^{3,4} | efficiency |
|-------------|----------------|----------------|-----------------------------|---------------------------------|------------|
| | (Vdc) | max (A) | max (W) | max (mVp-p) | typ (%) |
| VOF-225A-12 | 12 | 18.75 | 225 | 120 | 92 |
| VOF-225A-15 | 15 | 15 | 225 | 150 | 92 |
| VOF-225A-24 | 24 | 9.38 | 225 | 240 | 93 |
| VOF-225A-30 | 30 | 7.5 | 225 | 300 | 93 |
| VOF-225A-48 | 48 | 4.69 | 225 | 480 | 94 |
| VOF-225A-58 | 58 | 3.88 | 225 | 580 | 94 |

- Notes:
1. Maximum output power of 225 W with 13 CFM forced air cooling, and 120 W with natural convection cooling at 100 to 264 Vac.
 2. Combined output power of main output and fan supply shall not exceed the max power rating.
 3. Ripple is peak to peak with 20 MHz bandwidth and 10 μ F tantalum capacitor in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.
 4. Output ripple can be more than 10% of the output voltage at -40°C.
 5. All specifications are measured at Ta=25°C, nominal input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY


INPUT

| parameter | conditions/description | min | typ | max | units |
|---------------------------|--|------|------------|-----|--------|
| voltage | | 80 | | 264 | Vac |
| frequency | | 47 | | 63 | Hz |
| current | at 115 Vac, full load at 230 Vac, full load | | 2.2 1.1 | | A A |
| inrush current | at 230 Vac, cold start | | | 45 | A |
| leakage current | at 230 Vac | | 0.3 | | mA |
| power factor | at full load | 0.95 | | | |
| no load power consumption | | | | 0.5 | W |
| input fuse | 6.3 A/250 V time delay fuse (included) | | | | |

OUTPUT

| parameter | conditions/description | min | typ | max | units |
|----------------------------|---|-----|-------|-----|-------|
| initial set point accuracy | | | ±1 | | % |
| line regulation | | | ±0.5 | | % |
| load regulation | from 100% to 10% load | | ±1 | | % |
| start-up delay time | | | 2 | | s |
| rise time | at 115/230 Vac | | 55 | | ms |
| hold-up time | at 115/230 Vac | | 10 | | ms |
| adjustability ¹ | built in trim pot | | ±3 | | % |
| switching frequency | | 50 | | 300 | kHz |
| transient response | 25% step load change, at 0.1 A/μS slew rate, 50% duty cycle, 50/60 Hz, max excursion 4%, recovery time 5 ms | | | | |
| temperature coefficient | at 0~50°C | | ±0.05 | | %/°C |
| fan output ² | 12 Vdc / 500 mA | | | | |

Notes: 1. Adjustment potentiometer is located on the SMT side of the PCB.
2. Fan supply output voltage tolerance including set point accuracy, line and load regulation is ±10% and ripple and noise is less than 10%.

PROTECTIONS

| parameter | conditions/description | min | typ | max | units |
|--------------------------|------------------------|-----|-----|-----|-------|
| over voltage protection | hiccup, auto recovery | 110 | | 140 | % |
| over current protection | hiccup, auto recovery | 110 | | | % |
| short circuit protection | hiccup, auto recovery | | | | |

SAFETY & COMPLIANCE

| parameter | conditions/description | min | typ | max | units |
|---------------------------------|---|-----|----------------|-----|------------|
| isolation voltage | input to output input to ground | | 3,000 1,500 | | Vac Vac |
| safety approvals | EN 60950-1, IEC 60950-1 (ed.2), UL 60950 (ed.2), CSA C22.2 No. 60950-1 (ed.2), Class 1 SELV complies with LVD directive | | | | |
| safety class | class I | | | | |
| conducted emissions | EN 55032 Class B | | | | |
| radiated emissions | EN 55032 Class B (to be controlled in end system with external core (King core K5B RC 25 x 12 x 15-M in input cable (5 turns))) | | | | |
| input current harmonics | EN 61000-3-2, class D | | | | |
| voltage fluctuation and flicker | EN 61000-3-3, pass | | | | |
| ESD immunity | EN 61000-4-2, level 3, criterion A | | | | |

Notes: 3. The power supply is considered a component which will be installed into final equipment. The final equipment still must be tested to meet the necessary EMC directives.

SAFETY & COMPLIANCE



| parameter | conditions/description | min | typ | max | units |
|------------------------------------|------------------------------------|-----|-----------|-----|-------|
| radiated field immunity | EN 61000-4-3, level 3, criterion A | | | | |
| electrical fast transient immunity | EN 61000-4-4, level 3, criterion A | | | | |
| surge immunity | EN 61000-4-5, level 3, criterion A | | | | |
| conducted immunity | EN 61000-4-6, level 3, criterion A | | | | |
| magnetic field immunity | EN 61000-4-8, level 3, criterion A | | | | |
| voltage dips, interruptions | EN 61000-4-11, criterion A & B | | | | |
| MTBF | as per Telcordia-SR332-issue 3 | | 3,370,000 | | hours |
| RoHS | 2011/65/EU | | | | |

Notes: 1. The power supply is considered a component which will be installed into final equipment. The final equipment still must be tested to meet the necessary EMC directives.

ENVIRONMENTAL

| parameter | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|--------|-------|
| operating temperature | see derating curves | -40 | | 70 | °C |
| storage temperature | | -40 | | 85 | °C |
| operating humidity | non-condensing | 20 | | 90 | % |
| storage humidity | non-condensing | 20 | | 90 | % |
| operating altitude | | | | 16,000 | ft |

DERATING CURVES



MECHANICAL

| parameter | conditions/description | min | typ | max | units |
|---------------------|---|-----|-----|-----|-------|
| dimensions | 4.00 x 2.00 x 1.00 (101.60 x 50.80 x 25.40 mm) | | | | inch |
| weight | | | 200 | | g |
| cooling | external fan | | | | |
| J1 input connector | Mates with JST housing VHR-3M; pins SVH-41T-P1.1 or equivalent | | | | |
| J2 output connector | Screw Type: Accepts 28 ~ 16 AWG wire Header Type: Mates with JST housing VHR-6M; pins SVH-41T-P1.1 or equivalent | | | | |
| J3 fan connector | Mates with Tyco 640440-2 | | | | |

MECHANICAL DRAWINGS

Screw Type


units: inch [mm]

tolerance: ±0.04 [±1.0]

| J1 | |
|-----|----------|
| PIN | Function |
| 1 | L |
| 2 | NC |
| 3 | N |

| J2 | |
|-----|----------|
| PIN | Function |
| 1 | +VE |
| 2 | +VE |
| 3 | +VE |
| 4 | -VE |
| 5 | -VE |
| 6 | -VE |

| J3 | |
|-----|----------|
| PIN | Function |
| 1 | +FAN |
| 2 | -FAN |



MECHANICAL DRAWINGS (CONTINUED)

Header Type


units: inch [mm]

tolerance: ±0.04 [±1.0]

| J1 | |
|-----|----------|
| PIN | Function |
| 1 | L |
| 2 | NC |
| 3 | N |

| J2 | |
|-----|----------|
| PIN | Function |
| 1 | +VE |
| 2 | +VE |
| 3 | +VE |
| 4 | -VE |
| 5 | -VE |
| 6 | -VE |

| J3 | |
|-----|----------|
| PIN | Function |
| 1 | +FAN |
| 2 | -FAN |



REVISION HISTORY

| rev. | description | date |
|------|-----------------|------------|
| 1.0 | initial release | 09/01/2017 |

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.